

Model 375

Reduced Pressure Principle Assembly

Application

Designed for installation on potable water lines to protect against both backsiphonage and backpressure of contaminated water into the potable water supply. The Model 375 provides protection where a potential health hazard exists. Ideal for use where lead-free* valves are required.

Standards Compliance (Unless Otherwise Noted, Sizes 2 1/2" Thru 10")

- ASSE® Listed 1013
- · cUPC® Listed
- CSA® Certified B64.4 (2 1/2" thru 8")
- AWWA Compliant C511, and C550
- FM® Approved
- UL® Classified
- · C-UL® Classified
- NYC MEA 49-01-M Vol 2
- Approved by the Foundation for Cross Connection Control and Hydraulic Research at the University of Southern California.
- Meets the requirements of NSF/ANSI/CAN 61*
- *(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

Materials

Main valve body Ductile Iron ASTM A 536 Access covers Ductile Iron ASTM A 536

Coatings NSF Approved fusion epoxy finish

Internals Stainless steel, 300 Series

NORYL™

Fasteners Stainless Steel, 300 Series
Seal rings EPDM (FDA approved)
O-rings Buna Nitrile (FDA approved)
Springs Stainless Steel, 300 Series
Sensing line Stainless Steel, braided hose

Features

Sizes: 2 1/2", 3", 4", 6", 8", 10"

Maximum working water pressure 175 PSI

Maximum working water temperature 140°F

Hydrostatic test pressure 350 PSI

End connections (Grooved for steel pipe) AWWA C606

(Flanged) ANSI B16.42

Class 150

Attention:

Model 375 (flange body) and Model 375A (grooved body) have different lay lengths.











Options (Suffixes can be combined)

- with NRS shut-off valves (standard)
- ☐ FSC with epoxy coated wye type strainer (flanged only)
- ☐ G with grooved end NRS gate valves
- ☐ GF with grooved inlet connection and flanged outlet connection
- ☐ FG with flanged inlet connection and grooved outlet connection
- □ L less shut-off valves (flanged body connections)
- ☐ OSY with OS&Y gate valves☐ PI with Post Indicator gate valve
- ☐ BG with grooved end butterfly valves with integral
- supervisory switches


 *New Connected Products. Search ZCSM-PF on Zurn.com for details.


Accessories

- ☐ Connected Pressure Monitor (Model ZCSM-PF)*
- $\hfill \Box$ Connected Flow Meter Option (Model ZCSM-BTM must
- be ordered with Model ZCSM-PF)*
- ☐ OS & Y Gate valve tamper switch (OSY-40
- ☐ Air gap (Model AG)
- ☐ QT-SET Quick Test Fitting Set
- ☐ Repair kit (rubber only)
- ☐ Thermal expansion tank (Model XT)
- □ Wireless Monitor Retrofit Kit for conversion of existing model 375 (212-6-RFK-375W1, 8-10-RFK-375W1)

Relief Valve discharge port: 2 1/2" - 6" - 2.75 sq. in.

8" - 10" - 3.69 sq. in.






MODEL 3750SYG SHOWN ABOVE


Dimensions & Weights (do not include pkg.)

	MODEL 375 SIZE		DIMENSION (approximate)															WEIGHT																			
3			А		TH RFLY /ES	B LESS GATE VALVES		С		D		E OS&Y OPEN		E OS&Y CLOSED		E NRS GATE		E WITH BUTTERFLY VALVES		F		G		н		LESS SHUT- OFF VALVES		NRS GATE VALVES FLANGED		NRS GATE VALVES GROOVED		OS&Y GATE VALVES FLANGED		OS&Y GATE VALVES GROOVED		BUTTERFLY VALVES GROOVED	
in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kg	lbs.	kg	lbs.	kg	lbs.	kg	lbs.	kg	lbs.	kg
2 1/2	65	31	787	28	711	15 7/8	403	7 1/4	184	3 3/4	95	17 3/4	451	15 3/8	391	11 1/2	292	8 1/4	210	9 1/2	241	8 3/8	213	41 1/4	1048	60	27	162	73	144	65	170	77	152	69	132	60
3	80	32	813	28 1/2	724	15 7/8	403	7 1/4	184	3 3/4	95	20 1/4	514	17	432	12 3/4	324	8 1/2	216	9 1/2	241	8 3/8	213	42 3/4	1086	60	27	184	83	154	70	190	86	142	64	112	51
4	100	37 5/8	956	32 8/9	835	19 1/2	495	8	203	4 1/2	114	22 1/2	572	18 1/4	464	14 1/2	368	9	229	11	279	9 1/4	235	52 3/4	1340	98	44	278	126	260	118	288	131	274	124	182	83
6	150	44 5/8	1133	37 5/8	956	23 1/2	597	10	254	6	152	30 1/2	775	24 1/4	616	18	457	10 1/4	260	12 3/8	314	10 3/4	273	62 3/4	1594	175	79	459	208	431	196	475	215	449	204	293	133
8	200	60 7/8	1546	53 7/8	1369	37 3/4	959	11	279	10	254	37	940	28 1/2	724	21 1/8	537	12	305	15 3/8	391	16 3/4	425	85	2159	377	171	829	376	795	361	853	387	805	365	551	250
10	250	63 7/8	1622	57 7/8	1470	37 3/4	959	11	279	10	254	45 5/8	1159	34 3/4	883	24 3/4	629	13	330	15 3/8	391	16 3/4	425	93 1/4	2369	407	185	1167	529	1101	499	1225	556	1159	526	795	361

MODEL 375 2 1/2", 3" & 4" (STANDARD & METRIC)



MODEL 375 6", 8" & 10" (STANDARD & METRIC)



Typical Installation


Local codes shall govern installation requirements. Unless otherwise specified, the assembly shall be mounted at a minimum of 12" (305mm) and a maximum of 30" (762mm) above adequate drains with sufficient side clearance for testing and maintenance. The installation shall be made so that no part of the unit can be submerged.

ZCSM-PF CONNECTED PRESSURE MONITOR
ZCSM-BTM CONNECTED FLOW METER 12" MIN 30" MIN
DIRECTION OF FLOW ⇒

INDOOR INSTALLATION

(375OSY with ZCSM-PF Connected Pressure Monitor and ZCSM-BTM Connected Flow Meter accessories)

Ca	Capacity thru Schedule 40 Pipe (GPM)												
Pipe size	5 ft/sec	7.5 ft/sec	10 ft/sec	15 ft/sec									
2 1/2"	75	112	149	224									
3"	115	173	230	346									
4"	198	298	397	595									
6"	450	675	900	1351									
8"	780	1169	1559	2339									
10"	1229	1843	2458	3687									
12"	1763	2644	3525	5288									



OUTDOOR INSTALLATION

Specifications

www.zurn.com

The Reduced Pressure Principle Backflow Prevention Assembly shall be certified to NSF/ANSI/CAN 61, ASSE® Listed 1013, and supplied with full port gate valves. The main body and access cover shall be epoxy coated ductile iron (ASTM A 536), the seat ring and check valve shall be NORYL™, the stem shall be stainless steel (ASTM A 276) and the seat disc elastomers shall be EPDM. The checks and the relief valve shall be accessible for maintenance without removing the device from the line. The Reduced Pressure Principle Backflow Prevention Assembly shall be a ZURN WILKINS Model 375.